


# Anatomy of a Dropper



## BULB

Commonly made from Rubber or Thermoplastic Elastomer (TPE or Monprene)

## CLOSURE

18/400, 20/400 and 22/400 finishes are carried in our Continuous Stock line. Other sizes may be available in our Best Value line.

## PIPETTE

Made of plastic or glass. There are two ways to display pipette measurements: One is length only, measured from the gasket to the end of the pipette. This is displayed in inches, i.e. 2 7/16". The other is to show the diameter and complete length of the pipette in millimeters, i.e. 7mm x 66mm. Both measurements are generally included on McKernan's website. Make sure to always leave a space between the tip of the dropper and the bottom of the bottle to avoid breakage and to allow product to flow freely.

## PIPETTE STYLES:


### Bent Tip:



### Tapered Tip:



### Bulb Tip:



### Blunt Tip:



### Graduated: Can be combined with other styles



Call a sales rep at **1-800-787-7587** or search our website, **McKernan.com**, for our extensive collection of available droppers and accessories.



## ASK ABOUT FREE SAMPLES!